

Specifications



Photo is representative

Eaton V48M28T4916

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR943, 220°C, 150 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 150 kVA, WS60, 280B

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton General purpose ventilated transformer |
| CATALOG NUMBER | V48M28T4916 |
| UPC | 786680147272 |
| PRODUCT LENGTH/DEPTH | 31.5 in |
| PRODUCT HEIGHT | 51 in |
| PRODUCT WIDTH | 34.5 in |
| PRODUCT WEIGHT | 1220 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | DOE2016 Efficient |
| CERTIFICATIONS | UL Listed |
| CATALOG NOTES | 10 CFR Part 431 (2016) Efficient |



Powering Business Worldwide

Physical Attributes

COIL MATERIAL Aluminum

Performance Ratings

EFFICIENCY 10 CFR Part 431-2016 (DOE)

| | |
|--------------------------|--|
| ENCLOSURE | NEMA 2 |
| FRAME | FR943 |
| INSULATION | 220 °C |
| MOUNTING | Floor or wall, upright only |
| TAP SIZE | 2 at +2.5%, 4 at -2.5% |
| TYPE | Energy-efficient ventilated dry-type transformer |
| WIRING CONNECTION | 280B |

| | |
|---------------------------|----------------------|
| FREQUENCY RATING | 2016) |
| FREQUENCY RATING | 60 Hz |
| KVA RATING | 150 kVA |
| PRIMARY VOLTAGE | 480 V delta |
| SECONDARY VOLTAGE | 208Y/120 V |
| SOUND LEVEL | NEMA ST-20 |
| TEMPERATURE RISE | 150 °C rise |
| VOLT AMPERE RATING | 150 kVA |
| VOLTAGE RATING | 480 Vac-208Y/120 Vac |

Miscellaneous

| | |
|----------------------|------|
| WEATHERSHIELD | WS60 |
|----------------------|------|

Resources

BROCHURES

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - V48M28T4916](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton V48M28T4916

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR943, 220°C, 150 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 150 kVA, WS60, 280B

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton General purpose ventilated transformer |
| CATALOG NUMBER | V48M28T4916 |
| UPC | 786680147272 |
| PRODUCT LENGTH/DEPTH | 31.5 in |
| PRODUCT HEIGHT | 51 in |
| PRODUCT WIDTH | 34.5 in |
| PRODUCT WEIGHT | 1220 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| COMPLIANCES | DOE2016 Efficient |
| CERTIFICATIONS | UL Listed |
| CATALOG NOTES | 10 CFR Part 431 (2016) Efficient |



Powering Business Worldwide

Physical Attributes

COIL MATERIAL Aluminum

Performance Ratings

EFFICIENCY 10 CFR Part 431-2016 (DOE)

| | |
|--------------------------|--|
| ENCLOSURE | NEMA 2 |
| FRAME | FR943 |
| INSULATION | 220 °C |
| MOUNTING | Floor or wall, upright only |
| TAP SIZE | 2 at +2.5%, 4 at -2.5% |
| TYPE | Energy-efficient ventilated dry-type transformer |
| WIRING CONNECTION | 280B |

| | |
|---------------------------|----------------------|
| FREQUENCY RATING | 2016) |
| FREQUENCY RATING | 60 Hz |
| KVA RATING | 150 kVA |
| PRIMARY VOLTAGE | 480 V delta |
| SECONDARY VOLTAGE | 208Y/120 V |
| SOUND LEVEL | NEMA ST-20 |
| TEMPERATURE RISE | 150 °C rise |
| VOLT AMPERE RATING | 150 kVA |
| VOLTAGE RATING | 480 Vac-208Y/120 Vac |

Miscellaneous

| | |
|----------------------|------|
| WEATHERSHIELD | WS60 |
|----------------------|------|

Resources

BROCHURES

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - V48M28T4916](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

