Specifications



Photo is representative

Eaton V48M28T4916

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR943, 220°C, 150 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 150 kVA, WS60, 280B

General specifications	
PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T4916
UPC	786680147272
PRODUCT LENGTH/DEPTH	31.5 in
PRODUCT HEIGHT	51 in
PRODUCT WIDTH	34.5 in
PRODUCT WEIGHT	1220 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Physical Attributes	
COIL MATERIAL	Aluminum

Performance Ratings	
EFFICIENCY	10 CFR Part 431-2016 (DOE

ENCLOSURE	NEMA 2
FRAME	FR943
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
ТҮРЕ	Energy-efficient ventilated dry- type transformer
WIRING CONNECTION	280B

	2016)
FREQUENCY RATING	60 Hz
KVA RATING	150 kVA
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	150 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Miscellaneous		
WEATHERSHIELD	WS60	

Resources	
BROCHURES	Eaton's high-efficiency dry- type transformers Eaton's low-voltage dry-type
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T4916

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







