



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VP6375 60A 3W3P Plug *Hubbell--Killark*

Catalog Number	VP6375
Manufacturer	Hubbell--Killark
Description	60A 3 Pole 3 Wire Plug Assembly
Weight per unit	3.5 (lbs/each)
Product Category	Lighting Accessories

Features

amperage rating	60
Cord Type	G, W, S, SO, STO, or similar
Material	Body-Copper-free aluminum;Contacts-Brass;External screws-316 stainless steel;Spring tensioner-Patented beryllium copper
Number of Wires	3
Phase	3
Poles	3
Voltage Rating	250;600
Wire Size	6-4

Dimensions and Weight

Size	8.81 in x 3.68 in x 3.68 in
------	-----------------------------

Descriptions

Description	60A 3W3P PLUG
extra long description	KLRK VP6375 60A 3W3P PLUG ASSY
Long Description	60A 3 Pole 3 Wire Plug Assembly
Product Type	60A 3W3P Plug Assy
Special Features	VersaMate® metallic pin & sleeve plugs, receptacles, and in-line connectors are designed for heavy duty industrial use. These devices supply power to both fixed and portable electrical equipment including pumps, generators, welders, vacuums, blowers and similar apparatus. Suitable for indoor and outdoor use, as well as applications that include wet, cold, hosedown, hazardous and corrosive environments. Configurations are also available in reverse-service and polarized orientations.

Manufacturer Information

Brand	KILLARK
GTIN	00783936834450
Manufacturers Part Number	VP6375
series	VersaMate
UPC	783936834450



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Pin & Sleeve

Packaging

Carton	1
Weight Per each	3.5

Uses, Certifications, and Standards

Application	Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Re?neries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities
environmental conditions	Wet and hazardous locations
nema rating	NEMA 3, 4, 4X, 7BCD, 9FG
standard	UL, CSA