

WP2CH150QT

Wallpack with cutoff glare shield. All aluminum precision die cast construction with tempered glass lens. 30°. cutoff strip included. Lamp supplied.

Color: Bronze


Weight: 16.2 lbs

Lamp Info

Type: ED17
 Watts: 150W
 Shape/Size: N/A
 Base: N/A
 ANSI: N/A
 Hours: 10,000
 Lamp Lumens: 12,500
 Efficacy: 68 LPW

Ballast Info

Type: CWA-HPF QT
 120V: 1.1/1.6A
 208V: .6/.9A
 240V: .5/.8A
 277V: .5/.7A
 Input Watts: 185W
 Efficiency: 81%



Technical Specifications

UL Listing:

Suitable for wet locations. HID fixtures can be wired with 90°C supply wiring if supply wires are routed 3" away from ballast.

Housing:

Die cast aluminum, 1/2" NPS tapped holes top, both sides and back for conduit or photocontrol. Hinged refractor frame. Continuous silicone rubber gasket.

Reflector:

Specular anodized aluminum, removable for installation. Symmetrical light pattern maximizes distance between fixtures.

Cutoff Lens:

Tempered glass.

Refractor:

Prismatic optics designed to minimize glare and throw light down and out. Heat resistant borosilicate glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Quad Tap:

Fixture works with 120, 208, 240 and 277 Volts .

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.



WP2CH150QT

Wallpack with cutoff glare shield. All aluminum precision die cast construction with tempered glass lens. 30° cutoff strip included. Lamp supplied.

Color: Bronze


Weight: 16.2 lbs

Lamp Info

Type: ED17
 Watts: 150W
 Shape/Size: N/A
 Base: N/A
 ANSI: N/A
 Hours: 10,000
 Lamp Lumens: 12,500
 Efficacy: 68 LPW

Ballast Info

Type: CWA-HPF QT
 120V: 1.1/1.6A
 208V: .6/.9A
 240V: .5/.8A
 277V: .5/.7A
 Input Watts: 185W
 Efficiency: 81%



Technical Specifications

UL Listing:

Suitable for wet locations. HID fixtures can be wired with 90°C supply wiring if supply wires are routed 3" away from ballast.

Housing:

Die cast aluminum, 1/2" NPS tapped holes top, both sides and back for conduit or photocontrol. Hinged refractor frame. Continuous silicone rubber gasket.

Reflector:

Specular anodized aluminum, removable for installation. Symmetrical light pattern maximizes distance between fixtures.

Cutoff Lens:

Tempered glass.

Refractor:

Prismatic optics designed to minimize glare and throw light down and out. Heat resistant borosilicate glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Quad Tap:

Fixture works with 120, 208, 240 and 277 Volts .

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

