



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP34760R Cat 6 QC A/B Keystone Conn or (M10)

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | WP34760R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Quick Connect RJ45 Cat 6 T568 A/B Keystone Insert |
| Weight per unit | 0.0402 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Features

| | |
|------------|---|
| connection | RJ45 Female |
| insulation | Electrical Insulation Resistance: 500 (@ 100 VDC) |

Material, Color, and Finish

| | |
|--------|----------------|
| Color | Orange |
| Finish | Smooth plastic |

Dimensions and Weight

| | |
|------|--|
| Size | 0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30) |
|------|--|

Descriptions

| | |
|------------------------|---|
| Description | CAT 6 QC A/B KEYSTONE CONN OR (M10) |
| extra long description | OnQ WP34760R CAT 6 QC A/B KEYSTONE |
| Long Description | Quick Connect RJ45 Cat 6 T568 A/B Keystone Insert |
| Product Type | Cat 6 QC A/B Keystone Con or (M10) |
| Special Features | Quick Connect, Cat 6, RJ45, Keystone connector |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | LEGRAND-ON-Q |
| GTIN | 00804428036784 |
| Manufacturers Part Number | WP3476-OR |
| UPC | 804428036784 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | RJ45 Female Cat 6 Keystone Insert |

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 60 |
| Weight Per each | 0.0402 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential |
| Enclosure | Housing Material: High Impact Flame Retardant Plastic |
| environmental conditions | 0 to 93 (relative humidity, non-condensing) |
| Mounting | Keystone opening |
| standard | ANSI/TIA-568-C.2 |