



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



XJG24HDG 3/4X4" HDG Expn CPLG

Crouse-Hinds

Catalog Number	XJG24HDG
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series XJG Expansion Coupling, Rigid/Imc, Steel, Hot Dip Galvanized Finish, 4" Maximum Conduit Movement, 3/4" Trade Size
Weight per unit	2.2 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

dimensions	7.0000 IN X 2.2500 IN X 2.2500 IN
------------	-----------------------------------

Material, Color, and Finish

Finish	Hot Dip Galvanized
--------	--------------------

Descriptions

Description	3/4X4" HDG EXPN CPLG
extra long description	CRS-H XJG24 HDG 3/4 CND EXP JNT INT
Features	"XJG conduit expansion couplings for EMT and rigid/IMC are used with EMT, rigid metal conduit and IMC to couple together two sections of conduit subject to longitudinal movement. They are installed indoors or outdoors in long conduit runs to permit linear movement caused by thermal expansion and contraction to prevent damage to conduit supports and electrical systems in building or bridges. XJGs for rigid/IMC and EMT are also available with a hot dip galvanized finish (standard for trade sizes 1-1/4"" and
Long Description	Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 3/4" trade size
Product Type	3/4 CND Exp JNT Int GRD Max MVT 4 HDG

Manufacturer Information

Brand	Eaton
GTIN	00662276290167
Manufacturers Part Number	XJG24 HDG
UPC	662276290167

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	Expansion coupling



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.15

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	NEMA FB1 UL 514B, CSA C22.2